



Torque Adjustment or Re-calibration Procedure

Anoison preset torque value for customers. If it is not match your needs, you can adjust wrench to required torque setting as follows.

1. unpeel sticker from end of handle.
2. using a screwdriver, remove the end cap by a counter clockwise rotation.
3. Remove fastening screw from the handle using hex key.



4. insert the correct sized hex wrench.(see Hex Key table)



5. Rotate clockwise to increase the torque setting, counter clockwise to reduce.
6. Replace the end cap and tighten by a clockwise rotation. Be careful not to over tighten.

Part No.	Torque Wrench Description	Hex Key	
		mm	inches
ANO TW-001	For Thick Wall SMA/3.5mm/2.92mm/2.4mm/1.85mm Type Connectors	4	[5/32]
ANO TW-002	For Thick Wall SMA/3.5mm/2.92mm/2.4mm/1.85mm Type Connectors (Stainless steel)	4	[5/32]
ANO TW-003	For N Type Connectors	4	[5/32]
ANO TW-004	For N/7mm Type Connectors (Stainless steel)	4	[5/32]
ANO TW-005	For N Type Connectors	4	[5/32]
ANO TW-006	For N Type Connectors (Stainless steel)	4	[5/32]
ANO TW-007	For SC/N Type Connectors	4	[5/32]
ANO TW-008	For SC/N Type Connectors (Stainless steel)	4	[5/32]
ANO TW-009	For TNC Type Connectors (Stainless steel)	4	[5/32]
ANO TW-010	For TNC Type Connectors (Stainless steel)	4	[5/32]
ANO TW-011	For SMC Type Connectors	3	[7/64]
ANO TW-012	For SSMC Type Connectors	3	[7/64]
ANO TW-013	For SSMA Type Connectors	3	[7/64]
ANO TW-014	For SSMA Type Connectors (Stainless steel)	3	[7/64]
ANO TW-015	For SMA Hermetic Type Connectors	4	[5/32]
ANO TW-016	For 1mm Type Connectors	3	[7/64]
ANO TW-017	For TNC Type Connectors	4	[5/32]
ANO TW-018	For TNC Type Connectors	4	[5/32]
ANO TW-019	For Thin Wall SMA Type Connectors	4	[5/32]
ANO TW-020	For 7/16 Type Connector	4	[5/32]
ANO TW-021	For 7/16 Type Connector	4	[5/32]
ANO TW-043	For NEX10 Type Connector	4	[5/32]
ANO TW-087	For NEX10 Type Connector	5	[1/2]
ANO TW-088	For NEX10 Type Connector	5	[1/2]
ANO TW-090	For 4.3-10 Type Connector	5	[1/2]
ANO TW-091	For 4.3-10 Type Connector	5	[1/2]
ANO TW-092	For 4.1-9.5 Type Connector	5	[1/2]